





LEICA Fortis 6

Reticle and subtensions



Reticle L-4a

Table with dimensions on page 2





LEICA Fortis 6

Subtensions in cm/100 m

Riflescope		Leica Fortis 6 1 – 6 x 24 i	Leica Fortis 6 2 – 12 x 50 i	Leica Fortis 6 2.5 – 15 x 56 i
Reticle		L-4a	L-4a	L-4a
Bar spacing min.		1400.00	700.00	560.00
Magnification 10x	A	140.00	140.00	140.00
Magnification max.		233.33	116.67	93.33
Bar spacing min.		700.00	350.00	280.00
Magnification 10x	A/2	70.00	70.00	70.00
Magnification max.		116.67	58.33	46.67
Line thickness min.		5.00	2.50	2.00
Magnification 10x	B	0.50	0.50	0.50
Magnification max.		0.83	0.42	0.33
Bar thickness min.		24.00	12.00	9.60
Magnification 10x	C	2.40	2.40	2.40
Magnification max.		4.00	2.00	1.60
Dot diameter min.		15.00	7.50	6.00
Magnification 10x	D	1.50	1.50	1.50
Magnification max.		2.50	1.25	0.17

All specifications in centimeters on 100 meters (cm/100m)